



TN1810BF, Nylon Block Fork Terminal For 22 - 18 AWG

By Burndy
Catalog # [TN1810BF](#)

Nylon Block Fork Terminal For 22 - 18 AWG



Features

- Permits rapid, easy installation of the terminal under the screw head without complete removal of the screw
- Designed to fit securely into terminal blocks

Application

Power Connector

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	22 - 18 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	#18 AWG to #22 AWG

Configuration

Connector Type	Block Fork Terminal
----------------	---------------------

Dimensions

Dimension - Z inch	0.32 in
--------------------	---------

Dimension - L Length Overall mm	24 mm
Dimension - Pad Width inch	0.31 in
Dimension - Bolt Size fraction	#8 - #10
Dimension - Strip Length inch	3/16
Dimension - Stud Size inch	• #8 • #9 • #10
Dimension - Length Overall inch	0.95 in

General

Sub Brand	HYDENT
Insulation Type	Nylon
Physical Attribute - Tongue Type	Fork
Trade Name	HYDENT™
Plated	Y
Insulation	Y
Type	Fork Tongue
UPC 14 Digit GTIN	00781810524220
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810524220

Logistics

Minimum Pack Quantity	100
Carton Quantity	100
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)