



TN184F, Nylon Fork Terminal For 22 - 18 AWG

By Burndy
Catalog # [TN184F](#)

Nylon Fork Terminal For 22 - 18 AWG



Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

Specifications

Standards - RoHS Compliance	UI
Status	
Certification - CSA Approved	No

Conductor

Conductor Size	22 - 18 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Connector Type	Fork Terminal
----------------	---------------

Dimensions

Dimension - Z inch	0.24 in
Dimension - L Length Overall mm	19 mm
Dimension - Pad Width inch	0.23 in
Dimension - Bolt Size fraction	#3 - #4
Dimension - Strip Length inch	7/32
Dimension - Stud Size inch	• #3 • #4
Dimension - Length Overall inch	0.75 in

General

Insulation Type	Nylon
Physical Attribute - Tongue Type	Fork
Trade Name	INSULUG™
Plated	Y
Feature - Barrel Style	Shrouded
UPC 14 Digit GTIN	00781810530870
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810530870

Logistics

Minimum Pack Quantity	100
-----------------------	-----

Product Assets

[Catalog \[English\]](#)