



TP1014F, Vinyl Fork Terminal For 12 - 10 AWG

By Burndy
Catalog # [TP1014F](#)

Vinyl Fork Terminal For 12 - 10 AWG



Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	Yes

Conductor

Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size
Conductor Range	#12 AWG to #10 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Fork Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	4.000 in
Package Width	3.000 in

Package Weight	0.285 lb.
Dimension - Z inch	0.46 in
Dimension - L Length Overall mm	32 mm
Dimension - Pad Width inch	0.47 in
Package Height	1.500 in
Dimension - Hole Size fraction	13/50
Dimension - Bolt Size fraction	1/4
Dimension - Hole Size inch	0.26 in
Dimension - Strip Length inch	11/32 in
Dimension - Stud Size inch	1/4 in
Cable Insulation Diameter Maximum	0.260 in
Dimension - Length Overall inch	1.26 in

General

Insulation Type	Vinyl
Color Code	Yellow
Physical Attribute - Tongue Type	Fork
Trade Name	VINY LUG™
Plated	Y
Feature - Barrel Style	Shrouded
Insulation	Y
UPC 12 Digit	621945047105
UPC 14 Digit GTIN	00621945047105
Material	Copper
Plating Type	Tin
UPC	621945047105

Logistics

Minimum Pack Quantity	50
Carton Quantity	100
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)