



Q4A404N, 4-Conductor, 4-Hole, Heavy Duty Copper Lug

By Burndy
Catalog # [Q4A404N](#)



4-Conductor, 600-800 kcmil, 4-Hole, 1/2" Stud, 1.75" Spacing, Compact Design

Features

- QIKLUG™ Terminals feature compact size, high copper alloy terminal for joining cables to equipment pads or bars
- Each element accommodates a wide range of cable
- One-wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	600 kcmil-800 kcmil
Conductor - Copper Str Size	• 600 kcmil • 700 kcmil • 750 kcmil • 800 kcmil

Configuration

Physical Attribute - Number of Holes	4
Connector Type	Terminal

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Package Height	0.000 in
----------------	----------

Dimension - Height mm	0 mm
Dimension - B Length fraction	1-31/50 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	59 mm
Dimension - B Length inch	1.62 in
Dimension - D inch	1.66 in
Dimension - Hole Size mm	19 mm
Dimension - Hole Size inch	0.75 in
Dimension - Length Overall inch	2.31 in

General

Plated	N
Trade Name	QIKLUG™
UPC	781810079805
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810079805
UPC 14 Digit GTIN	00781810079805

Logistics

Minimum Pack Quantity	2
Pallet Quantity	1
Carton Quantity	1

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)