



QA262B, 2-Hole, Heavy Duty Copper Terminal

By Burndy
Catalog # [QA262B](#)

1/0-2/0 Str, 2-Hole, 3/8" Stud, 1" Spacing, Single Clamping Element, Compact Design



Features

- QIKLUG™ Terminals feature compact size, high copper alloy terminal for joining cables to equipment pads or bars
- Each element accommodates a wide range of cable
- One-wrench installation

Application

For Copper Cable

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 1/0 • 2/0 AWG
Conductor Size	1/0-2/0 AWG
Conductor - Copper Str Navy Size Range	100 (61) Navy-125 (61) Navy
Conductor - Copper Str Navy Size	• 100 (61) Navy • 125 (61) Navy
Conductor Type	• CU C Str-Size • CU C Str Navy-Size
Conductor - Copper Str Size Range	1/0 -2/0 AWG

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	2
Connector Type	Single Clamp

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Dimension - Pad Width inch	0.81 in
Package Height	0.000 in
Dimension - Height mm	28.4 mm
Dimension - Hole Size fraction	13/32
Dimension - Height inch	1.12 in
Dimension - Height fraction	1-3/16
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.00 in
Package Width	0.000 in
Dimension - L Length Overall mm	77 mm
Dimension - Hole Size mm	11 mm
Dimension - Hole Size inch	0.44 in
Dimension - Stud Size inch	3/8
Dimension - Bolt Size fraction	3/8
Dimension - B Length fraction	22/25 in
Dimension - Width inch	0.09 in
Dimension - B Length inch	0.88 in
Dimension - D inch	1.94 in
Dimension - N inch	0.44 in
Dimension - Length Overall inch	3.00 in

Force Related

Installation Torque Recommended in-lb	180 LBS/in
---------------------------------------	------------

General

Product Family	MECHANICAL
Trade Name	QIKLUG™
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	No
Sub Brand	QIKLUG
Product Type	Terminal
UPC	781810314289
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810314289
UPC 14 Digit GTIN	00781810314289

Logistics

Minimum Pack Quantity	1
Pallet Quantity	6720

Carton Quantity	12	Product Assets
Operational		Catalog [English]
Temperature Rating	194	Installation Manual [English]
 A Hubbell brand		© 2026 Hubbell Incorporated. All rights reserved BRDY-QA262B-SPEC-EN REV 7/2026