

TP106BF, Vinyl Block Fork Terminal For 12 - 10 AWG

By Burndy
Catalog # [TP106BF](#)



Vinyl Block Fork Terminal For 12 - 10 AWG

Features

- Permits rapid, easy installation of the terminal under the screw head without complete removal of the screw
- Designed to fit securely into terminal blocks

Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size
Conductor Range	#12 AWG to #10 AWG

Configuration

Connector Type	Block Fork Terminal
----------------	---------------------

Dimensions

Package Length	4.250 in
Package Width	3.000 in
Package Weight	0.260 lb.
Dimension - Z inch	0.29 in

Dimension - L Length Overall mm	26 mm
Dimension - Pad Width inch	0.30 in
Package Height	3.000 in
Dimension - Bolt Size fraction	#4 - #6
Dimension - Strip Length inch	19/64 in
Dimension - Stud Size inch	#4 - #6
Cable Insulation Diameter Maximum	0.260 in
Dimension - Length Overall inch	1.02 in

General

Sub Brand	HYDENT
Insulation Type	Vinyl
Physical Attribute - Tongue Type	Block Fork
Trade Name	VINYLUG™
Plated	Y
Feature - Barrel Style	Shrouded
Insulation Type	Y
UPC 12 Digit	Fork Tongue
UPC 14 Digit GTIN	781810524312
Material	781810524312
Plating Type	Copper
UPC	Tin
	781810524312

Logistics

Minimum Pack Quantity	50
Carton Quantity	100
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)