



QA312B, 2-Hole, Heavy Duty Copper Terminal

By Burndy

Catalog # [QA312B](#)

250-350 kcmil, 2-Hole, 3/8" Stud, 1" Spacing, Single Clamping Element, Compact Design



Features

- QIKLUG™ Terminals feature compact size, high copper alloy terminal for joining cables to equipment pads or bars
- Each element accommodates a wide range of cable
- One-wrench installation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 250 kcmil • 300 kcmil • 350 kcmil
Conductor Size	250-350 kcmil
Conductor - Copper Str Navy Size Range	250 (61) Navy-350 (91) Navy
Conductor - Copper Str Navy Size	• 250 (61) Navy • 300 (91) Navy • 350 (91) Navy
Conductor Type	• CU C Str-Size • CU C Str Navy-Size
Conductor - Copper Str Size Range	250 kcmil-350 kcmil

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	2
Connector Type	Single Clamp

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Dimension - Pad Width inch	1.19 in
Package Height	0.000 in
Dimension - Height mm	42.9 mm
Dimension - Hole Size fraction	7/16
Dimension - Height inch	1.69 in
Dimension - Height fraction	1-11/16
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.00 in
Package Width	0.000 in
Dimension - L Length Overall mm	84 mm
Dimension - Hole Size mm	11 mm
Dimension - Hole Size inch	0.44 in
Dimension - Stud Size inch	3/8
Dimension - Bolt Size fraction	3/8
Dimension - D inch	2.00 in
Dimension - N inch	0.44 in
Dimension - Length Overall inch	3.31 in

Force Related

Installation Torque Recommended in-lb	325 LBS/in
---------------------------------------	------------

General

Trade Name	QIKLUG™
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
UPC	781810315408
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810315408
UPC 14 Digit GTIN	00781810315408

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)

[Installation Manual \[English\]](#)



A Hubbell brand