



TP146BF, Vinyl Block Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # [TP146BF](#)



Vinyl Block Fork Terminal For 16 - 14 AWG

Features

- Permits rapid, easy installation of the terminal under the screw head without complete removal of the screw
- Designed to fit securely into terminal blocks

Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	16 - 14 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	#16 AWG to #14 AWG

Configuration

Connector Type	Block Fork Terminal
----------------	---------------------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.

Dimension - Z inch	0.30 in
Dimension - L Length Overall mm	23 mm
Dimension - Pad Width inch	0.25 in
Package Height	0.000 in
Dimension - Bolt Size fraction	#4 - #6
Dimension - Strip Length inch	13/64 in
Dimension - Stud Size inch	#4 - #6
Cable Insulation Diameter Maximum	0.190 in
Dimension - Length Overall inch	0.93 in

General

Sub Brand	HYDENT
Insulation Type	Vinyl
Physical Attribute - Tongue Type	Block Fork
Trade Name	VINYLUG™
Plated	Y
Feature - Barrel Style	Shrouded
Insulation Type	Y
Type	Fork Tongue
UPC 12 Digit	781810524343
UPC 14 Digit GTIN	00781810524343
Material	Copper
Plating Type	Tin
UPC	781810524343

Logistics

Minimum Pack Quantity	100
Carton Quantity	100
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)