



QB4C, 1-Hole, Heavy Duty Copper Terminal

By Burndy

Catalog # [QB4C](#)

#8-4 AWG Copper, 1-Hole, 1/4" Stud, Right Angled (Side Entry)
Connector



Features

- Side Entry terminal
- Joins a range of cable at right angles to terminal blocks
- One-wrench installation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG
Conductor Size	8-4 AWG
Number Of Conductors	1
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	8 AWG-4 AWG

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Clamping Elements	1
Connector Type	Right Angle

Dimensions

Dimension - Pad Width fraction	11/16 in
Dimension - Pad Width inch	0.63 in
Package Height	0.000 in
Dimension - Height mm	26.2 mm

Dimension - Hole Size fraction	9/32
Dimension - Height inch	1.03 in
Dimension - Height fraction	1-1/32
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	35 mm
Dimension - Hole Size mm	7 mm
Dimension - Hole Size inch	0.28 in
Dimension - Stud Size inch	1/4
Dimension - Stud Size fraction	1/4
Dimension - Bolt Size fraction	1/4
Dimension - B Length fraction	3/4 in
Dimension - Width mm	18 mm
Dimension - Width inch	0.70 in
Dimension - B Length inch	0.75 in
Dimension - D inch	0.84 in
Dimension - N inch	0.38 in
Dimension - Length Overall inch	1.38 in

Force Related

Installation Torque	110 LBS/in
Recommended in-lb	

General

Trade Name	QIKLUG™
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
UPC	781810324202
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810324202

Logistics

Minimum Pack Quantity	33
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)

