



TP148F, Vinyl Fork Terminal, 16-14 AWG, #6-8 Stud

By Burndy

Catalog # [TP148F](#)

Vinyl Fork Terminal For 16 - 14 AWG, #6-8 Stud, Fork Design for Faster Installation



Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	• 16 AWG • 14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	16 AWG - 14 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Fork Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Pad Width inch	0.31 in
Package Height	0.000 in
Dimension - Hole Size fraction	8/47
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	22 mm
Dimension - Hole Size inch	0.17 in
Dimension - Strip Length inch	13/64
Dimension - Stud Size inch	• #6 • #8
Dimension - Bolt Size fraction	#6 - #8
Dimension - B Length fraction	13/50 in
Dimension - Z inch	0.26 in
Dimension - B Length inch	0.26 in
Dimension - Length Overall inch	0.86 in
Cable Insulation Diameter Maximum	0.180 in

General

Product Family	COMPRESSION
Insulation Type	Vinyl
Trade Name	VINYLUG™
Insulation	Y
Feature - Barrel Style	Shrouded
Plated	Yes
Color Code	Blue
Physical Attribute - Tongue Type	Fork
Sub Brand	VINYLUG
Product Type	Terminal
UPC	781810712689
Type	TP-F
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810712689
UPC 14 Digit GTIN	00781810712689

Logistics

Minimum Pack Quantity	100
Pallet Quantity	99999
Carton Quantity	1200

Product Assets

[Catalog \[English\]](#)



A Hubbell brand