



TP1610F, Vinyl Fork Terminal For 22 - 16 AWG

By Burndy
Catalog # [TP1610F](#)



Vinyl Fork Terminal For 22 - 16 AWG

Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Size	20 AWG 18 AWG 16 AWG
Conductor Size	22 - 16 AWG
Conductor Type	CU C Str-Size
Conductor Range	#20 AWG to #22 AWG 16 AWG to 18 AWG

Configuration

Physical Attribute - Number of Holes	1
--------------------------------------	---

Connector Type	Fork Terminal
----------------	---------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	24 mm
Dimension - Pad Width inch	0.41 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.20 in
Dimension - Strip Length inch	1/4 in
Dimension - Stud Size inch	#10
Dimension - Z inch	0.31 in
Dimension - Bolt Size fraction	#10
Cable Insulation Diameter Maximum	0.145 in
Dimension - Length Overall inch	0.95 in

General

Insulation Type	Vinyl
Trade Name	VINYLUG™
Insulation	Y
Sub Brand	VINYLUG
Color Code	Red
Physical Attribute - Tongue Type	Fork
Plated	Y
Feature - Barrel Style	Shrouded
Type	TP-F
UPC 12 Digit	781810714881
UPC 14 Digit GTIN	00781810714881
Material	Copper
Plating Type	Tin
UPC	781810714881

Logistics

Minimum Pack Quantity	100
Carton Quantity	1200
Pallet Quantity	99999



A Hubbell brand