



QDA4CW, 1-Hole, Heavy Duty Round Tongue, Tinned

By Burndy
Catalog # [QDA4CW](#)

#8-4 AWG Str, 1-Hole, 3/8" Stud, Rounded Tongue, Heavy Duty Copper Lug, Tin Dip Plating



Features

- Compact, high copper alloy terminal
- Joins a wide range of cable to equipment studs
- Provides low contact resistance when tripped between two contact nuts
- One-wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Navy Size Range	23 (7) Navy-40 (19) Navy
Conductor - Copper Str Navy Size	• 23 (7) Navy • 30 (19) Navy • 40 (19) Navy
Conductor Type	• CU C Str-Size • CU C Str Navy-Size
Conductor - Copper Str Size Range	8 AWG-4 AWG
Conductor - Copper Str Size	• 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG

Configuration

Physical Attribute - Number of Screws	1
---------------------------------------	---

Physical Attribute - Number of Holes	1
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.00 in
Dimension - Height mm	18.3 mm
Dimension - Height inch	0.72 in
Dimension - Height fraction	18/25 in
Dimension - Width mm	25 mm
Dimension - Width inch	1.00 in
Dimension - L Length Overall mm	48 mm
Dimension - Cross Flats inch	0.56 in
Dimension - Hole Size mm	11 mm
Dimension - Hole Size inch	0.44 in
Dimension - Length Overall inch	1.88 in
Dimension - Stud Size inch	3/8

Force Related

Installation Torque Recommended in-lb	110 LBS/in
---------------------------------------	------------

General

Physical Attribute - Screw Type Plated	Hexagonal Bolt Y
Trade Name	QIKLUG™
UPC	781810052068
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Tin - Hot Dipped
UPC 14 Digit GTIN	00781810052068

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)