



TP186FBG25, Vinyl Fork Terminal For 22 - 18 AWG

By Burndy
Catalog # [TP186FBG25](#)



Vinyl Fork Terminal For 22 - 18 AWG

Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor Size	22 - 18 AWG
----------------	-------------

Conductor Type	CU C Str-Size
----------------	---------------

Configuration

Connector Type	Fork Terminal
----------------	---------------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Package Height	0.000 in
Dimension - Bolt Size fraction	#22-#18

General

Insulation Type	Vinyl
Trade Name	HYDENT™
Plated	Y
Insulation	Y
UPC 12 Digit	781810486573
UPC 14 Digit GTIN	00781810486573
Material	Copper
Plating Type	Tin
UPC	781810486573

Logistics

Minimum Pack Quantity	5
Carton Quantity	5
Pallet Quantity	12000

Product Assets

[Catalog \[English\]](#)