

QPX2828, Mech. Parallel Clamp for Cu, Mult. Configurations

By Burndy
Catalog # [QPX2828](#)



Run #1-4/0 AWG, Tap #1-4/0 AWG, Capable of Tee, Cross, Parallel, Butt and Tap Configurations

Features

- VERSITAP™ Type QPX Parallel Clamps for copper are capable of Tee, Cross, Parallel, Butt and Tap configurations
- Range-taking, only 10 connectors are required to accommodate conductor sizes from #6 Stranded to 1000 kcmil
- Edges are rounded for easy taping

Application

For Tee, Cross, Parallel, Butt, and Tap Connections, Copper

Specifications

Buy American Compliant	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	EX
Status	
Certification - UL Listed Direct	No
Burial	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Run Range	1 AWG-4/0 AWG
Conductor - Copper Str Run	• 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor Type	• CU C Str-Run • CU C Str-Tap
Conductor - Copper Str Tap Range	1 AWG-4/0 AWG
Conductor - Copper Str Tap	• 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG

Configuration

Connector Type	Universal Clamp
----------------	-----------------

Dimensions

Package Height	0.000 in
Dimension - Height mm	60.5 mm
Dimension - Height inch	2.38 in
Dimension - Height fraction	2-3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	46 mm
Dimension - Width fraction	1-13/16 in
Dimension - Width mm	46 mm
Dimension - Width inch	1.81 in
Dimension - Length Overall inch	1.81 in

Force Related

Installation Torque Recommended	240 LBS/in in-lb
---------------------------------	------------------

General

Product Family	MECHANICAL
Trade Name	VERSITAP™
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	No
Sub Brand	VERSITAP
Product Type	Run/Tap
UPC	781810342503
Type	QPX
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810342503

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2100
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)