



QPX2C2C, Mech. Parallel Clamp for Cu, Mult. Configurations

By Burndy
Catalog # QPX2C2C



Run #6-#2 AWG, Tap #6-#2 AWG, Capable of Tee, Cross, Parallel, Butt and Tap Configurations

Features

- VERSITAP™ Type QPX Parallel Clamps for copper are capable of Tee, Cross, Parallel, Butt and Tap configurations
- Range-taking, only 10 connectors are required to accommodate conductor sizes from #6 Stranded to 1000 kcmil
- Edges are rounded for easy taping

Application

For Tee, Cross, Parallel, Butt And Tap Connections, Copper

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	EX
Status	
Certification - UL Listed Direct	No
Burial	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Nominal Diameter	0.179, 0.182, 0.184, 0.199, 0.206, 0.219, 0.223, 0.225, 0.230, 0.232, 0.246, 0.258, 0.260, 0.276, 0.290, 0.310, 0.320, 0.326
Conductor - Copper Str Run Range	6 AWG-2 AWG
Conductor - Copper Str Run	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor Type	• CU C Str-Run • CU C Str-Tap
Conductor - Copper Str Tap Range	6 AWG-2 AWG
Conductor - Copper Str Tap	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG

Configuration

Physical Attribute - Number of Screws	2
Connector Type	Universal Clamp

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Package Height	0.000 in
Dimension - Height mm	38.1 mm
Dimension - Height inch	1.5
Dimension - Height fraction	1-1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	33 mm
Dimension - Width fraction	1-3/8 in
Dimension - B Length fraction	1/3 in
Dimension - Width mm	35 mm
Dimension - Width inch	1.38
Dimension - B Length inch	0.31 in
Dimension - Length Overall inch	1.31 in

Force Related

Installation Torque Recommended in-lb	180 LBS/in
---------------------------------------	------------

General

Product Family	MECHANICAL
Trade Name	VERSITAP™
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	No
Sub Brand	VERSITAP
Product Type	Run/Tap
UPC	781810341506
Type	QPX
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810341506
UPC 14 Digit GTIN	00781810341506

Logistics

Minimum Pack Quantity 1
Pallet Quantity 1
Carton Quantity 12

Temperature Rating 194

Product Assets

[Catalog \[English\]](#)

Operational



A Hubbell brand