



QQA262, Twin Clamping, 2-Hole, Heavy Duty Copper Terminal

By Burndy

Catalog # [QQA262](#)

1/0-2/0 AWG Cu Str, 2-Hole, 3/8" Stud, 1" Spacing, 2 Clamping Elements



Features

- QIKLUG™ Terminals feature compact size, high copper alloy terminal for joining cables to equipment pads or bars
- Each element accommodates a wide range of cable
- One-wrench installation

Application

For Joining Copper Cable To Equipment Pads Or Bars

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 1/0 • 2/0 AWG
Conductor Size	1/0-2/0 AWG
Conductor - Copper Str Navy Size Range	100 (61) Navy-125 (61) Navy
Conductor - Copper Str Navy Size	• 100 (61) Navy • 125 (61) Navy
Conductor Type	• CU C Str-Size • CU C Str Navy-Size
Conductor - Copper Str Size Range	1/0 -2/0 AWG

Configuration

Physical Attribute - Number of Screws	2
Physical Attribute - Number of Holes	2
Connector Type	Duel Clamp

Dimensions



A Hubbell brand

Dimension - Pad Width inch	0.81 in
Package Height	0.000 in
Dimension - Height mm	28.7 mm
Dimension - Height inch	1.13 in
Dimension - Height fraction	1.125 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.00 in
Package Width	0.000 in
Dimension - L Length Overall mm	106 mm
Dimension - Hole Size mm	10 mm
Dimension - Hole Size inch	0.41 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	1.94 in
Dimension - N inch	0.44 in
Dimension - Length Overall inch	4.19 in

Force Related

Installation Torque	180 LBS/in
Recommended in-lb	

General

Trade Name	QIKLUG™
Physical Attribute - Screw Type Plated	Hexagonal Bolt N
Sub Brand	MECHANICAL CONNECTOR, QIKLUG
UPC	781810325858
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810325858

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)