



UCK1UL, Tin-Plated Cast Copper Alloy Interlocking-Finger Design Parallel Clamp

By Burndy
Catalog # [UCK1UL](#)

Interlocking finger design accommodates large range of conductor sizes.Tin-plated, cast of high copper alloy and clamped with silicon bronze DURUM bolt,wrench size:1/2.

Features

- Tin-plated cast copper alloy featuring interlocking-finger design
- Accommodates large range of conductor sizes
- Clamped with silicon bronze bolts

Application

For Use With Aluminum Or Galvanized Steel Strand To Copper Or Copper Bonded Steel Wire, Grounding For The Cable TV Industry

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size B	6 Str
Conductor - Copper Solid Size B	6 Sol
Conductor - Galvanized Steel Str Size Range	1/4 in -5/16 in

Dimensions

Package Height	0.000 in
Dimension - Height mm	36.5 mm
Dimension - Height inch	1.4375 in



Dimension - Height fraction	1-7/16 in
Package Weight	0.000 lb.
Dimension - Width mm	37 mm
Dimension - Width inch	1.4375 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	25 mm
Dimension - Width fraction	1-7/16 in
Dimension - Length Overall inch	1 in

Force Related

Installation Torque	180 LBS/in
Recommended in-lb	

General

Plated	Y
Sub Brand	TAPIT
UPC	781810120750
Type	UC-K, Universal
Material	Aluminum
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810120750
UPC 14 Digit GTIN	00781810120750

Logistics

Pallet Quantity	1
Carton Quantity	150

Product Assets

[Catalog \[English\]](#)