

QQA31, Twin Clamping, 1-Hole, Heavy Duty Copper Terminal

By Burndy
Catalog # [QQA31](#)



250-300 kcmil Cu, 1-Hole, 1/2" Stud, 2 Clamping Elements, 1-Wrench Installation

Features

- QIKLUG™ Terminals feature compact size, high copper alloy terminal for joining cables to equipment pads or bars
- Each element accommodates a wide range of cable
- One-wrench installation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 250 kcmil • 300 kcmil • 350 kcmil
Conductor Size	250-300 KCMIL
Conductor - Copper Str Navy Size Range	250 (61) Navy-350 (91) Navy
Conductor - Copper Str Navy Size	• 250 (61) Navy • 300 (91) Navy • 350 (91) Navy
Conductor Type	• CU C Str-Size • CU C Str Navy-Size
Conductor - Copper Str Size Range	250 kcmil-350 kcmil

Configuration

Physical Attribute - Number of Screws	2
Physical Attribute - Number of Holes	1
Connector Type	Duel Clamp

Dimensions

Dimension - Pad Width inch	1.19 in
Package Height	0.000 in
Dimension - Height mm	42.9 mm
Dimension - Height inch	1.69 in
Dimension - Height fraction	1.6896551724137931 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	105 mm
Dimension - Hole Size mm	13 mm
Dimension - Hole Size inch	0.53 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	1.38 in
Dimension - N inch	0.69 in
Dimension - Length Overall inch	4.13 in

Force Related

Installation Torque	325 LBS/in
Recommended in-lb	

General

Trade Name	QIKLUG™
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
UPC	781810006009
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810006009

Logistics

Minimum Pack Quantity	32
Pallet Quantity	216
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)