



UCK2UL, Interlocking-finger Parallel Clamp,
#6 AWG Sol/Str Cu, 1/4"-5/16" Galvanized
Steel Guy Wire, Tin-Plated Copper

By Burndy
Catalog # [UCK2UL](#)

Interlocking-finger Parallel Clamp

Features

- Tin-plated cast copper alloy featuring interlocking-finger design
- Accommodates large range of conductor sizes
- Clamped with silicon bronze bolts

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size B	6 Str
Conductor - Copper Solid Size B	6 Sol
Conductor - Galvanized Steel Str Size Range	1/4 in -5/16 in

Dimensions

Package Height	0.000 in
Dimension - Height mm	36.5 mm
Dimension - Height inch	1.4375 in
Dimension - Height fraction	1-7/16 in
Package Weight	0.000 lb.



Dimension - Width mm	37 mm
Dimension - Width inch	1.4375 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	25 mm
Dimension - Width fraction	1-7/16 in
Dimension - Length Overall inch	1 in

Force Related

Installation Torque	180 LBS/in
Recommended in-lb	

General

Plated	Y
UPC	781810120828
Material	Aluminum
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810120828
UPC 14 Digit GTIN	00781810120828

Logistics

Minimum Pack Quantity	1
Pallet Quantity	14400
Carton Quantity	150

Product Assets

[Catalog \[English\]](#)