


QR34, Mech. Heavy Duty Copper Splice Reducer

By Burndy
Catalog # [QR34](#)

Mechanical Splice / Reducer, 400-500 kcmil Cu, Compact Style,
1-Wrench Installation



Features

- Type QR QIKLINK™ splice or reducer features a neat, compact, easy to tape installation
- One-wrench installation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	• 400 kcmil • 450 kcmil • 500 kcmil
Conductor Size	400-500 kcmil
Conductor - Copper Str Size B	• 400 kcmil • 450 kcmil • 500 kcmil
Conductor - Copper Str Size A Range	400 kcmil-500 kcmil
Conductor Type	• CU C Str-Size A • CU C Str-Size B • CU C Solid-Size A • CU C Solid-Size B
Conductor - Copper Str Size B Range	400 kcmil-500 kcmil

Configuration

Physical Attribute - Number of Screws	2
Connector Type	In-Line

Dimensions

Package Height	0.000 in
Dimension - Height mm	49.3 mm
Dimension - Height inch	2.06 in
Dimension - Height fraction	2-1/16 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	78 mm
Dimension - Width fraction	1-7/16 in
Dimension - B Length fraction	1-3/8 in
Dimension - Width mm	37 mm
Dimension - Width inch	1.44 in
Dimension - B Length inch	1.38 in
Dimension - Length Overall inch	3.06 in

Force Related

Installation Torque	375 LBS/in
Recommended in-lb	

General

Trade Name	QIKLINK™
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
UPC	781810334690
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810334690

Logistics

Minimum Pack Quantity	2
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)