

Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S2GBP41A12B2](#)



Substation Connectors

Features

- Streamlined rigid spacer for large range of cables
- 1 bolt per clamping module
- EHV Rated: Self-Shielding up to 550kV

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 795 kcmil • 800 kcmil • 874 kcmil
Conductor - AL Str Size Range	795 kcmil-874 kcmil
Conductor - ACSR Str Size	• 715.5 (24/7) Stilt kcmil • 715.5 (26/7) Starling kcmil
Conductor - ACSR Str Size Range	715.5 (24/7) Stilt kcmil-715.5 (26/7) Starling kcmil

Configuration

Connector Type	Spacer
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Dimension - Width mm	102 mm
Dimension - Width inch	4.00 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	341 mm
Dimension - B Length inch	4.00 in
Dimension - Length Overall inch	13.44 in

General

Plated	N
UPC	781810269114
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810269114
UPC 14 Digit GTIN	00781810269114

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)