




UH153CG9, Substation Copper Bus Support

By Burndy
Catalog # UH153CG9

Copper Bus Connectors



Features

- Type UH Copper Bus Supports for Supporting Copper Tube to Base
- High copper alloy bus support for mounting tube on a post or pedestal type insulator
- Single bolt allows rotation to any angle
- Rotate cap 180 degrees for slip or rigid fit
- Supplied with hardware for mounting to cap of insulator
- Suffix -B on the catalog number denotes base mounting hardware is supplied

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Number Of Conductors	1
Conductor - Connection Combination	Base to Tube
Conductor Type	• CU Tube Std-Size • CU Tube EH-Size
Conductor - Copper Tube Std Size Range	1 IPS IPS
Conductor - Copper Tube Std Size	1 IPS IPS
Conductor - Copper Tube EH Size Range	1 IPS IPS

Conductor - Copper Tube EH Size	1 IPS IPS
---------------------------------	-----------

Configuration

Connector Type	Bus Support
----------------	-------------

Dimensions

Bolt Circle Diameter	3.00 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
Fitting Type	Slip or Rigid
UPC	621945049338
Type	Cable or Tube to Insulator Bus Supports
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	621945049338
UPC 14 Digit GTIN	00621945049338

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)