

Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S2GBP483A](#)



Two Conductor 18 IN Spacer, 2050 kcmil ACSR, 2000 kcmil-2250 kcmil AAC

Features

- Streamlined rigid spacer for large range of cables
- 1 bolt per clamping module
- EHV Rated: Self-Shielding up to 550kV

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 2000 kcmil • 2250 kcmil
Conductor - AL Str Size Range	2000 kcmil-2250 kcmil
Conductor - ACSR Str Size	2050 kcmil
Conductor - ACSR Str Size Range	2034.5 (72/7) Mockingbird kcmil

Configuration

Connector Type	Spacer
----------------	--------

Dimensions

Dimension - Height mm	0 mm
Dimension - Width mm	76 mm
Dimension - Width inch	3.00 in
Dimension - B Length inch	3.00 in
Dimension - Diameter Min Size inch	1.632 in
Dimension - Diameter Max Size inch	1.737 in

Force Related

Installation Torque	480 lbs-in
Recommended in-lb	

General

Plated	N
UPC	781810365991
Material	Aluminum Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810365991
UPC 14 Digit GTIN	00781810365991

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)