




VP4440, V-Bolt Connector for Flex or Extra Flex Conductor

By Burndy
Catalog # [VP4440](#)



V-Bolt Connector for Flex or Extra Flex Conductor

Features

- Type VP, Parallel Groove Clamp for Copper
- Multiple V-Bolt connector especially suited for flexible or extra flexible conductors
- Made of high strength, high conductivity copper
- Clamping elements accommodate a range of conductor sizes in either groove
- V-bolts provide high pressure and compress the conductor over long contact area
- Also suitable for jumper connections

Specifications

Certification - ETL	No
Certification - UL Recognized	Yes
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	• 750 kcmil • 800 kcmil • 850 kcmil • 900 kcmil • 1000 kcmil
Conductor - Copper Str Size B	• 500 kcmil • 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil • 800 kcmil
Conductor - Copper Str Size A Range	750 kcmil-1000 kcmil
Conductor - Copper Str Size B Range	500 kcmil-800 kcmil

Configuration

Connector Type	V-Bolt
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Height mm	127 mm
Dimension - Height inch	5.00 in
Dimension - Height fraction	5 in
Package Weight	0.000 lb.
Dimension - Width mm	81 mm
Dimension - Width inch	3.19 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	102 mm
Dimension - Width fraction	3-1/4 in
Dimension - Length Overall inch	4.00 in

General

Plated	N
UPC	781810013632
Prefilled Oxide Inhibitor	N
Material	Copper Alloy
Plating Type	Unplated
UPC 14 Digit GTIN	00781810013632

Logistics

Minimum Pack Quantity	2
Pallet Quantity	360
Carton Quantity	3

Product Assets

[Catalog \[English\]](#)