



SN10, Nylon Splice For 12 - 10 AWG

By Burndy
Catalog # [SN10](#)

Nylon Splice For 12 - 10 AWG



Features

- Seamless tubing, high quality design without seams to split
- Electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Tin plating provides durable long-lasting resistance to corrosion
- Positive center wire stop for proper depth of wire insertion
- Nylon is locked into position

Application

For Heavy Duty Application Requirements

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL486
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	• 12 AWG • 10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	12 AWG-10 AWG

Configuration

Connector Type	Seamless Butt Splice
----------------	----------------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	42 mm
Dimension - Outside Diameter	0.22 in
Dimension - Strip Length	5/16 in
Dimension - Diameter Max Size	0.22 in
Dimension - Length Overall	1.64 in
Cable Insulation Diameter Maximum	0.220 in

General

Insulation Type	Nylon
Trade Name	INSULINK™
Insulation	Y
Plated	Y
Color Code	Yellow
Sub Brand	INSULINK
UPC	781810737026
Type	SN
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810737026
UPC 14 Digit GTIN	00781810737026

Logistics

Pallet Quantity	72000
Carton Quantity	300

Operational

Temperature Rating	105
--------------------	-----

Product Assets

[Catalog \[English\]](#)