



SN14B, Nylon Splice For 16 - 14 AWG

By Burndy
Catalog # [SN14B](#)

Nylon Splice For 16 - 14 AWG

Features

- Tin plated copper brazed butt seam
- Smooth funnel entry for easy wire insertion
- Nylon insulation offers high dielectric strength and stability

Application

For Heavy Duty Application Requirements

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	16 - 14 AWG
Conductor - Copper Str Size Range	16 - 14 AWG

Configuration

Connector Type	Brazed Seam Butt Splice
----------------	-------------------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.15 in
Dimension - L Length Overall mm	32 mm
Package Height	0.000 in
Dimension - Strip Length inch	7/32 in
Dimension - Length Overall inch	1.25 in

General

Sub Brand	INSULINK
Insulation Type	Nylon
Color Code	Blue
Trade Name	INSULINK™
Plated	Y
Insulation	Y
Type	SN
UPC 12 Digit	781810525098
UPC 14 Digit GTIN	00781810525098
Material	Copper
Plating Type	Tin
UPC	781810525098

Logistics

Minimum Pack Quantity	100
Carton Quantity	100
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)