



Substation - Copper V Type T Connector

By Burndy
Catalog # [VT4434](#)

V Style Connectors

Features

- High copper alloy T-connector for cable run, cable tap
- V-Bolt clamping elements accommodate large range of cable and are particularly suited for extra flexible cable
- 1-wrench installation

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	No
Conductor	
Conductor - Copper Str Run Range	750 kcmil-1000 kcmil
Conductor - Copper Str Run	• 750 kcmil • 800 kcmil • 850 kcmil • 900 kcmil • 1000 kcmil
Conductor - Connection Combination	Cable to Cable
Conductor Type	• CU C Str-Run • CU C Str-Tap
Conductor - Copper Str Tap Range	300 kcmil-500 kcmil
Conductor - Copper Str Tap	• 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil

Configuration

Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Number of Run Conductors	1
Connector Type	T-Connector

Dimensions

Package Height	0.000 in
Dimension - Height mm	84.8 mm
Dimension - Height inch	3.34 in
Package Weight	0.000 lb.
Dimension - Width mm	57 mm
Dimension - Width inch	2.25 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	111 mm
Dimension - Length Overall inch	4.38 in

Force Related

Installation Torque Recommended in-lb	3.6 LBS/in
---------------------------------------	------------

General

Plated	N
Trade Name	VARITAP™
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
UPC	781810078433
Type	Bolted Tees
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810078433
UPC 14 Digit GTIN	00781810078433

Logistics

Minimum Pack Quantity	6
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)