




VV2A4644N45, Substation - Copper V Type Terminal

By Burndy
Catalog # [VV2A4644N45](#)

V Style Connectors



Features

- Type VVA VARILUG Terminals, for Copper Cable to Pad
- Type VVA features twin elements to secure against vibration and flexing
- High copper alloy terminal for joining a wide range of cable to equipment pads or bar
- Particularly suitable for use on extra flexible cable
- One-wrench installation

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	1000 kcmil-1500 kcmil

Conductor - Copper Str Size	• 1000 kcmil • 1250 kcmil • 1300 kcmil • 1500 kcmil
-----------------------------	---

Configuration

Connector Type	Terminal
----------------	----------

Dimensions

Dimension - Pad Width inch	4.00 in
Dimension - Height mm	0 mm

General

Plated	N
Trade Name	VARILUG™
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810450604
Type	Bolted Lugs & Terminals
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810450604
UPC 14 Digit GTIN	00781810450604

Product Assets

[Catalog \[English\]](#)