



T108F, Fork Terminal, 12-10 AWG, #6-8 Stud

By Burndy

Catalog # [T108F](#)

Uninsulated Fork Terminal For 12 - 10 AWG, #6-8 Stud, Fork Design
Provides Faster Installation



Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

Application

For Control Wiring And Other Standard Duty Applications

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	• 14 AWG • 10 AWG (Str.) • 12 AWG (Sol.) • 10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	14 AWG - 10 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Fork Terminal

Dimensions

Dimension - Pad Width inch	0.31 in
Package Height	0.000 in
Dimension - Hole Size fraction	8/47
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	20 mm
Dimension - Hole Size inch	0.17 in
Dimension - Strip Length inch	11/32
Dimension - Stud Size inch	• #6 • #8
Dimension - Bolt Size fraction	#6 - #8
Dimension - B Length fraction	17/50 in
Dimension - Z inch	0.27 in
Dimension - B Length inch	0.34 in
Dimension - Diameter Max Size inch	0.12 in
Dimension - Length Overall inch	0.80 in
Cable Insulation Diameter Maximum	0.120 in

General

Product Family	COMPRESSION
Trade Name	HYLUG™
Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
Plated	Yes
Physical Attribute - Tongue Type	Fork
Sub Brand	HYLUG
Product Type	Terminal
UPC	781810722060
Type	T-F
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810722060
UPC 14 Digit GTIN	00781810722060

Logistics

Minimum Pack Quantity	50
Pallet Quantity	99999
Carton Quantity	600

Product Assets

[Catalog \[English\]](#)



A Hubbell brand