



T1414F, Uninsulated Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # [T1414F](#)



Uninsulated Fork Terminal For 16 - 14 AWG

Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor Size	16 - 14 AWG
Conductor Type	- CU C Solid-Size - CU C Str-Size
Conductor Range	#20 AWG to #14 AWG

Configuration

Connector Type	Fork Terminal
----------------	---------------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Z inch	0.39 in
Dimension - L Length Overall mm	23
Dimension - Pad Width inch	0.47 in
Package Height	0.000 in
Dimension - Bolt Size fraction	1/4
Dimension - Strip Length inch	9/32
Dimension - Stud Size inch	1/4 in
Dimension - Length Overall inch	0.92 in

General

Physical Attribute - Tongue Type	Fork
Trade Name	HYLUG™
Plated	Y
Feature - Barrel Style	Shrouded
UPC 12 Digit	781810722466
UPC 14 Digit GTIN	00781810722466
Material	Copper
Plating Type	Tin
UPC	781810722466

Logistics

Minimum Pack Quantity	100
Carton Quantity	1200
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)