


VV2A46CG1, Substation - Copper V Type Terminal

By Burndy
Catalog # [VV2A46CG1](#)

V Style Connectors



Features

- Type VVA VARILUG Terminals, for Copper Cable to Pad
- Type VVA features twin elements to secure against vibration and flexing
- High copper alloy terminal for joining a wide range of cable to equipment pads or bar
- Particularly suitable for use on extra flexible cable
- One-wrench installation

Application

Substation

Specifications

Standards - RoHS Compliance	EX
Status	
Certification - CSA Approved	No

Conductor

Conductor Type	CU C Str-Size
Conductor - Copper Str Size	1000 kcmil-1500 kcmil
Conductor - Copper Str Size Range	
Conductor - Copper Str Size	• 1000 kcmil • 1250 kcmil • 1300 kcmil • 1500 kcmil

Configuration

Connector Type	Terminal
----------------	----------

Dimensions

Dimension - Pad Width inch	3.50 in
Dimension - Height mm	101.6 mm
Dimension - Height inch	4.00 in
Dimension - Width mm	171 mm
Dimension - Width inch	6.75 in
Dimension - L Length Overall mm	222 mm
Dimension - Length Overall inch	8.75 in

General

Plated	N
Trade Name	VARILUG™
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810457801
Type	Bolted Lugs & Terminals
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810457801
UPC 14 Digit GTIN	00781810457801

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)