


TN106LF, Nylon Locking Fork Terminal, 12-10 AWG, #4-6 Stud

By Burndy
Catalog # [TN106LF](#)

Nylon Locking Fork Terminal For 12 - 10 AWG, #4-6 Stud, Fast Installation with Security



Features

- Locking fork tongue design allows fast installation, screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking fork is made from copper alloy, permits many installations while maintaining proper spring retention of forks

Application

Power Connector

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	No
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	12 - 10 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	#10 AWG to #12 AWG

Configuration

Connector Type	Locking Fork Terminal
----------------	-----------------------

Dimensions

Dimension - Pad Width inch	0.30 in
----------------------------	---------

Package Height	1.500 in
Dimension - Bolt Size fraction	#4 - #6
Package Weight	0.221 lb.
Package Length	4.000 in
Package Width	3.000 in
Dimension - Z inch	0.29 in
Dimension - L Length Overall mm	26 mm
Dimension - Length Overall inch	1.02 in
Dimension - Strip Length inch	11/32
Dimension - Stud Size inch	• #4 • #6

General

Plated	Yes
Product Family	COMPRESSION
Insulation Type	Nylon
Trade Name	INSULUG™
Physical Attribute - Tongue Type	Fork
Sub Brand	HYDENT
Product Type	Terminal
UPC	781810524138
Type	TN
Insulation	Y
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810524138

Logistics

Minimum Pack Quantity	1
Pallet Quantity	99999
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)