



VVA464NCG2, Substation - Copper V Type Terminal

By Burndy
Catalog # [VVA464NCG2](#)

V Style Connectors



Features

- Type VVA VARILUG Terminals, for Copper Cable to Pad
- Type VVA features twin elements to secure against vibration and flexing
- High copper alloy terminal for joining a wide range of cable to equipment pads or bar
- Particularly suitable for use on extra flexible cable
- One-wrench installation

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Cable to Flat
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	1000 kcmil-1500 kcmil
Conductor - Copper Str Size	• 1000 kcmil • 1250 kcmil • 1300 kcmil • 1500 kcmil

Configuration

Connector Type

Terminal

Dimensions

Dimension - Pad Width inch	3.50 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Dimension - Width mm	83 mm
Dimension - Width inch	3.25 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	222 mm
Dimension - B Length inch	2.00 in
Dimension - Length Overall inch	8.75 in

General

Plated	N
Trade Name	VARILUG™
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810456224
Type	Bolted Lugs & Terminals
Material	Bronze Alloy
Plating Type	Unplated
UPC 12 Digit	781810456224
UPC 14 Digit GTIN	00781810456224

Logistics

Minimum Pack Quantity	4
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)