

Substation - Copper Expansion Coupler

By Burndy
Catalog # [XP1919HC](#)



Substation Connectors

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Connection	Tube to Tube
Combination	
Conductor Type	• CU Tube Std-Size • CU Tube EH-Size
Conductor - Copper Tube Std Size Range	2 1/2 IPS
Conductor - Copper Tube Std Size	2 1/2 IPS

Configuration

Physical Attribute - Pad Orientation	Straight
Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Number of Run Conductors	1
Connector Type	Couplers

Dimensions

Dimension - Height mm	215.9 mm
Dimension - Height inch	8.50 in
Dimension - Width mm	133 mm
Dimension - Width inch	5.25 in
Dimension - L Length Overall mm	330 mm
Dimension - B Length inch	4.00 in
Dimension - Length BB inch	4.00 in
Dimension - Length Overall inch	13.00 in

Force Related

Installation Torque	480 LBS/in
Recommended in-lb	

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
UPC	781810242865
Type	Tube to Tube Couplers
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810242865
UPC 14 Digit GTIN	00781810242865

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)