



TN1410LF, Nylon Locking Fork Terminal, 16-14 AWG, #8-10 Stud

By Burndy
Catalog # [TN1410LF](#)



Nylon Locking Fork Terminal For 16 - 14 AWG, #8-10 Stud, Fast Installation with Security

Features

- Locking fork tongue design allows fast installation - screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking fork is made from a copper alloy and permits many installations while maintaining proper spring retention of forks

Application

Power Connector

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	16 - 14 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	#14 AWG to #16 AWG

Configuration

Connector Type	Locking Fork Terminal
----------------	-----------------------

Dimensions

Dimension - Pad Width inch	0.32 in
----------------------------	---------

Package Height	0.000 in
Dimension - Bolt Size fraction	#8 - #10
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.30 in
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.95 in
Dimension - Strip Length inch	7/32
Dimension - Stud Size inch	• #8 • #10

General

Plated	Yes
Product Family	COMPRESSION
Insulation Type	Nylon
Trade Name	INSULUG™
Physical Attribute - Tongue Type	Fork
Sub Brand	HYDENT
Product Type	Terminal
UPC	781810524176
Type	TN
Insulation	Y
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810524176

Logistics

Minimum Pack Quantity	100
Pallet Quantity	1
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)