

Substation - Copper Expansion Coupler

By Burndy
Catalog # [XP5656](#)



Cast Copper Alloy Expansion Coupler , 1-1/4 IN IPS, 11.56 IN L

Features

- Cast Copper Alloy Expansion Coupler
- 1-1/4" IPS
- 11.56" Length

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	• CU Tube Std-Size • CU Tube EH-Size
Conductor - Copper Tube Std Size Range	1 1/4 IPS
Conductor - Copper Tube Std Size	1 1/4 IPS
Conductor - Copper Tube EH Size Range	1 1/4 IPS
Conductor - Copper Tube EH Size	1 1/4 IPS

Configuration

Connector Type	Couplers
----------------	----------

Dimensions

Package Height	0.000 in
Dimension - Height mm	148 mm
Dimension - Height inch	5.82 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	294 mm
Dimension - Length Overall inch	11.56 in

Force Related

Installation Torque Recommended in-lb	480 in-lb
---------------------------------------	-----------

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810487815
Type	Tube to Tube Couplers
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810487815
UPC 14 Digit GTIN	00781810487815

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)