



TN181OLF, Nylon Locking Fork Terminal For 22 - 18 AWG

By Burndy
Catalog # [TN181OLF](#)

Nylon Locking Fork Terminal For 22 - 18 AWG



Features

- Locking fork tongue design allows fast installation - screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking fork is made from a copper alloy and permits many installations while maintaining proper spring retention of forks

Application

Power Connector

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	22 - 18 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	#18 AWG to #22 AWG

Configuration

Connector Type	Locking Fork Terminal
----------------	-----------------------

Dimensions

Package Length	0.000 in
----------------	----------

Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Z inch	0.32 in
Dimension - L Length Overall	24 mm
Dimension - Pad Width inch	0.31 in
Package Height	0.000 in
Dimension - Bolt Size fraction	#8 - #10
Dimension - Strip Length inch	7/32
Dimension - Stud Size inch	• #8 • #10
Dimension - Length Overall	0.95 in
inch	

General

Sub Brand	HYDENT
Insulation Type	Nylon
Physical Attribute - Tongue	Fork
Type	
Trade Name	INSULUG™
Plated	Y
Insulation	Y
Type	TN
UPC 14 Digit GTIN	00781810524237
Material	Copper
Plating Type	Unplated
UPC	781810524237

Logistics

Minimum Pack Quantity	100
Carton Quantity	100
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)