



Electric Hydraulic Pump, Remote Crimpers & Cutters, 10K psi

By Burndy
Catalog # [Y10AC9](#)

Electric Hydraulic Pump, Use with Remote Crimpers & Cutters, 10,000 psi

Features

- Easy to carry and transport
- Factory set relief valve
- 100,000+ life cycles
- Sealed electric pendant switch with 10-foot cord

Application

Pumping

Specifications

Standards - RoHS Compliance EX
Status

Current

Current Draw Max 11 Amperes

Dimensions

Length 8.25 in
Weight 28 lb.
Height 14.38 in
Width 6.5 in



Dimensions

8.25 in x 6.5 in x 14.38 in

General

Application - For Use On Use with 10,000 psi Remote Hydraulic Crimpers and Cutters
Tool Type Pump, Electric Hydraulic
Product Type Pump, Hydraulic 10,000 PSI
UPC 781810467299
Type Pumps
UPC 12 Digit 781810467299
UPC 14 Digit GTIN 00781810467299

Logistics

Package Contents Pump only

Operational

Power Source

- 5/8 HP 115V-AC Motor
- 10000 RPM

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)