



Y10AC9 Hydraulic OEM Pump Kit with Foot Switch, 7 Qts, 10,000 psi, 5/8 HP 115V-AC 60/50 Hz 11 Amps Full Load

By Burndy
Catalog # [Y10AC9OEM](#)

Y10AC9 Pump Kit, Foot Switch, 7 Quarts

Features

- Audible Pop Off valve
- Autoretract
- Foot pedal switch with protective guard
- Large capacity reservoir

Application

Pumping

Specifications

Standards - RoHS Compliance EX
Status

Current

Current Draw Max 11 Amperes

Dimensions

Length 12.37 in
Width 10.25 in
Weight 67.60 lb.
Height 15.86 in

Dimensions 12.37 in x 10.25 in x 15.86 in

General

Application - For Use On Use with 10,000 psi Remote Hydraulic Crimpers and Cutters Pump
Type 781810463017
UPC 12 Digit 00781810463017
UPC 14 Digit GTIN
Tool Type Pump, Electric Hydraulic
UPC 781810463017

Logistics

Package Contents Pump, Foot Control
Minimum Pack Quantity 1

Operational

Power Source • 5/8 HP 115V-AC Motor
 • 50/60 Cycle

Product Assets

[Catalog \[English\]](#)