



Full Cycle Ratchet Crimper, #22-8 AWG, Embossment

By Burndy
Catalog # [Y8MRB1](#)



Full Cycle Ratchet Crimper, #22 - 8 AWG, Indenter markings for inspectability

Features

- Light weight
- Each indenter has unique identifying marks for inspectability
- Fully enclosed, protected ratchet mechanism does not allow the handles to be opened until full ratchet cycle is completed
- Inspection gauges available to check each groove

Application

Crimping

Specifications

Standards - RoHS Compliance	EX
Status	
Buy American Compliant	No

Conductor

Crimping Ranges	#22 - #8 AWG
-----------------	--------------

Dimensions

Package Height	0.000 in
Length	10.56 in
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Weight	1.21 lb.
Height	1.04 in
Width	3.5 in
Dimensions	10.56 in x 3.5 in x 1.04 in

General

Application - For Use On	#22-8 AWG Uninsulated Terminals and Splices
Trade Name	HYTOOL™
Sub Brand	HYTOOL
Tool Type	Full Cycle Ratchet Crimper
Product Type	Ratchet and Small Hand Tools
Die Type	Permanent Die Grooves
UPC	781810031100
UPC 12 Digit	781810031100
UPC 14 Digit GTIN	00781810031100

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

[Catalog \[English\]](#)