



YA1CA9DT, Comp. Term., AL, 1 AWG, 1-Hole, Soldered Seam

By Burndy
Catalog # [YA1CA9DT](#)

Aluminum Compression Terminal, 1 AWG, 2-Hole, 1/2" Stud, 1.75" Spacing, Soldered Seam, Tin Plated, AL9CU, UL/CSA

Features

- UL486A-486B Listed and CSA Certified
- Aluminum terminals are dual rated to accommodate both copper and aluminum wire and are indicated with AL-CU on the connector - AL9CU is UL Listed 90°C, up to 35kV, AL7CU is UL Listed 75°C, up to 35kV
- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damage of the wire strands during insertion
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with wire size, die index, color code, and crimp location bands
- Factory pre-filled with PENETROX Type A13 oxide inhibitor
- Color coded end caps are factory inserted in the barrels to match the die color code and prevent foreign materials from entering the barrel
- Aluminum oxidation is not easily detected but causes resistance in a connection, it is imperative the proper preparation takes place prior to making an aluminum-to-aluminum connection

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Material	ALUMINUM / COPPER
Wire Size	1 AWG
Conductor - AL Str Size	1 AWG
Conductor - AL Str Size Range	1 AWG



Conductor - Copper Str Size	1 AWG
Conductor Size	1 AWG
Conductor Type	CODE
Conductor - Copper Str Size Range	1 AWG

Configuration

Number of Holes	2
Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	DUAL RATED

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.88 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	115 mm
Dimension - Outside Diameter inch	0.54 in
Dimension - Thread Size	1/2
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	7/8 in
Dimension - Z inch	0.73 in
Dimension - B Length inch	0.91 in
Dimension - D inch	3.11 in
Dimension - N inch	0.63 in
Dimension - Bolt Size inch	0.5
Dimension - Length Overall inch	4.52 in

General

Trade Name	HYLUG™
Die Index	471
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Gold
Physical Attribute - Tongue	Standard
Type	
Sub Brand	HYLUG
UPC	781810268414
Type	YA-A
Material	Aluminum
Plating Type	Tin - Electro Plated
Finish Type	Electro Tin plated
UPC 12 Digit	781810268414

UPC 14 Digit GTIN00781810268414

Logistics

Minimum Pack Quantity	20
Pallet Quantity	9280
Carton Quantity	20

Operational

Temperature Rating	194
--------------------	-----

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[English\]](#)



A Hubbell brand