

TP1410BF, Vinyl Block Fork Terminal, 16-14 AWG, #8-10 Stud

By Burndy
Catalog # [TP1410BF](#)



Vinyl Block Fork Terminal For 16 - 14 AWG, #8-10 Stud, Rapid, Easy Installation

Features

- Permits rapid, easy installation of the terminal under the screw head without complete removal of the screw
- Designed to fit securely into terminal blocks

Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	16 - 14 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	#16 AWG to #14 AWG

Configuration

Connector Type	Block Fork Terminal
----------------	---------------------

Dimensions

Dimension - Pad Width inch	0.32 in
Package Height	0.000 in
Dimension - Bolt Size fraction	#8 - #10

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.30 in
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.95 in
Cable Insulation Diameter	0.180 in
Maximum	
Dimension - Strip Length inch	13/64 in
Dimension - Stud Size inch	#8 - #10

General

Feature - Barrel Style	Shrouded
Plated	Yes
Product Family	COMPRESSION
Insulation Type	Vinyl
Trade Name	VINYLU TM
Physical Attribute - Tongue Type	Block Fork
Sub Brand	HYDENT
Product Type	Terminal
UPC	781810524336
Type	Fork Tongue
Insulation	Y
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810524336
UPC 14 Digit GTIN	00781810524336

Logistics

Minimum Pack Quantity	100
Pallet Quantity	99999
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)