

TP1414, Vinyl Ring Terminal For 16 - 14 AWG

By Burndy
Catalog # [TP1414](#)



Vinyl Ring Terminal For 16 - 14 AWG

Features

- Expanded insulation support accepts standard and large wire diameters providing lower inventory requirements and greater flexibility
- Funnel entry for easy wire insertion
- Manufactured of pure electrolytic copper to provide maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove serrations in the inner barrel provides added holding strength and better conductivity

Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	16 - 14 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	#16 AWG to #14 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Pad Width inch	0.40 in
Package Height	0.000 in
Dimension - Hole Size fraction	10/37
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	27 mm
Dimension - Hole Size inch	0.27 in
Dimension - Strip Length inch	13/64 in
Dimension - Stud Size inch	1/4 in
Dimension - Bolt Size fraction	1/4
Dimension - Z inch	0.36 in
Dimension - Length Overall inch	1.05 in
Cable Insulation Diameter Maximum	0.190 in

General

Insulation Type	Vinyl
Trade Name	VINYLUG™
Insulation	Y
Feature - Barrel Style	Shrouded
Plated	Y
Color Code	Blue
Physical Attribute - Tongue Type	Ring
Sub Brand	VINYLUG
UPC	781810713044
Type	Ring Tongue
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810713044
UPC 14 Digit GTIN	00781810713044

Logistics

Pallet Quantity	99999
Carton Quantity	1200

Product Assets

[Catalog \[English\]](#)