



TP168F, Vinyl Fork Terminal For 22 - 16 AWG

By Burndy
Catalog # [TP168F](#)



Vinyl Fork Terminal For 22 - 16 AWG

Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	22 - 16 AWG
Conductor Type	- CU C Solid-Size - CU C Str-Size
Conductor Range	#20 AWG to #22 AWG 16 AWG to 18 AWG

Configuration

Physical Attribute - Number of Holes	1
--------------------------------------	---

Connector Type	Fork Terminal
----------------	---------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Pad Width inch	0.31 in
Package Height	0.000 in
Dimension - Hole Size fraction	9/53
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	22 mm
Dimension - Hole Size inch	0.17 in
Dimension - Strip Length inch	1/4 in
Dimension - Stud Size inch	#8
Dimension - Bolt Size fraction	#8
Dimension - Z inch	0.26 in
Dimension - Length Overall inch	0.86 in
Cable Insulation Diameter Maximum	0.145 in

General

Insulation Type	Vinyl
Trade Name	VINYLUG™
Insulation	Y
Feature - Barrel Style	Shrouded
Plated	Y
Color Code	Red
Physical Attribute - Tongue Type	Fork
Sub Brand	VINYLUG
UPC	781810714683
Type	TP-F
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810714683
UPC 14 Digit GTIN	00781810714683

Logistics

Minimum Pack Quantity	100
Pallet Quantity	99999
Carton Quantity	1200



A Hubbell brand