

TP1810FBG25, Vinyl Fork Terminal For 22 - 18 AWG

By Burndy
Catalog # [TP1810FBG25](#)



Vinyl Fork Terminal For 22 - 18 AWG

Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor Size	22 - 18 AWG
Conductor - Copper Str Size	20 AWG 18 AWG 16 AWG
Conductor - Copper Str Size Range	20 AWG - 16 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Fork Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length fraction	13/50 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.26 in
Dimension - Pad Width inch	0.36 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/5
Dimension - Bolt Size fraction	#8 - #10
Dimension - Hole Size inch	0.20 in
Dimension - Stud Size inch	#8 #10
Dimension - Length Overall inch	0.74 in

General

Insulation Type	Vinyl
Trade Name	HYDENT™
Plated	Y
Feature - Barrel Style	Shrouded
Insulation	Y
UPC 12 Digit	781810486535
UPC 14 Digit GTIN	00781810486535
Material	Copper
Plating Type	Tin
UPC	781810486535

Logistics

Minimum Pack Quantity	5
Carton Quantity	5
Pallet Quantity	11440

Product Assets

[Catalog \[English\]](#)