


UC4W28, Copper Parallel Groove Clamp

By Burndy
Catalog # [UC4W28](#)

CU Parallel Groove Clamp accommodates large number of CU
Conductors, Conductor: 4 Sol. - 4/0 Str. (Either Groove)



Features

- Type UC connector accommodates large range of conductors in either groove, reducing inventory requirements
- Interlocking finger design provides firm grip with maximum contact length
- High strength, corrosion resistant silicon bronze hardware

Application

For Range Of Copper

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 4 AWG
	• 3 AWG
	• 2 AWG
	• 1 AWG
	• 1/0
	• 2/0 AWG
	• 3/0 AWG
	• 4/0 AWG
Conductor - Copper Str Size A	4 - 4/0
Conductor - Copper Str Size B	4 - 4/0
Conductor - Copper Str Size A Range	4 - 4/0
Conductor - Copper Solid Size	4 AWG
Conductor - Copper Solid Size Range	4 AWG
Conductor - Copper Str Size Range	4 AWG-4/0 AWG

Conductor - Copper Str Size B Range	4 - 4/0
-------------------------------------	---------

Dimensions

Package Height	0.000 in
Dimension - Height mm	50.8 mm
Dimension - Height inch	1.93 in
Dimension - Height fraction	1-15/16 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Width fraction	1-3/4 in
Dimension - B Length fraction	2-1/8 in
Dimension - B Length inch	2.125 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
---------------------------------------	------------

General

Product Family	Utility Overhead & Underground Distribution>Mechanical Bolted Tap Connectors>Parallel Clamps
Plated	No
Sub Brand	TAPIT
Product Type	Mechanical
UPC	781810012888
Type	UC
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810012888

Logistics

Minimum Pack Quantity	2
Pallet Quantity	720
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)