




UH173B, Substation Copper Bus Support

By Burndy
Catalog # [UH173B](#)

Copper Bus Connectors



Features

- Type UH Copper Bus Supports for Supporting Copper Tube to Base
- High copper alloy bus support for mounting tube on a post or pedestal type insulator
- Single bolt allows rotation to any angle
- Rotate cap 180 degrees for slip or rigid fit
- Supplied with hardware for mounting to cap of insulator
- Suffix -B on the catalog number denotes base mounting hardware is supplied

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Number Of Conductors	1
Conductor - Connection Combination	Base to Tube
Conductor Type	• CU Tube Std-Size • CU Tube EH-Size
Conductor - Copper Tube Std Size Range	1 1/2 IPS IPS
Conductor - Copper Tube Std Size	1 1/2 IPS IPS
Conductor - Copper Tube EH Size Range	1 1/2 IPS IPS
Conductor - Copper Tube EH Size	1 1/2 IPS IPS

Configuration

Connector Type Bus Support

Dimensions

Bolt Circle Diameter	3.00 in
Dimension - G inch	2.50 in
Package Height	0.000 in
Dimension - Height mm	96.8 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	3.81 in
Package Weight	0.000 lb.
Dimension - Width mm	97 mm
Dimension - Width inch	3.81 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - Hole Size inch	0.56 in

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
Fitting Type	Slip or Rigid
One Wrench Installation	Y
UPC	781810077795
Type	Cable or Tube to Insulator Bus Supports
Mounting Hardware	1/2-13 x 1 1/2" LG
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810077795
Hardware Type	Base mounting kit (w nuts)
UPC 14 Digit GTIN	00781810077795

Logistics

Minimum Pack Quantity	2
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)