

UH225, Substation Copper Bus Support, 4" IPS, 5" Bolt Dia, 5/8" Bolt

By Burndy
Catalog # [UH225](#)



Cast Cu Alloy Bus Support, 4" IPS, 5" Bolt Dia, 5/8" Bolt.

Features

- Type UH Copper Bus Supports for Supporting Copper Tube to Base
- High copper alloy bus support for mounting tube on a post or pedestal type insulator
- Single bolt allows rotation to any angle
- Rotate cap 180 degrees for slip or rigid fit
- Supplied with hardware for mounting to cap of insulator
- Suffix -B on the catalog number denotes base mounting hardware is supplied

Application

Substation

General

Catalog Number	UH225
Fitting Type	Slip or Rigid
Hardware Type	Cap mounting kit (w/o nuts)
Installation Torque	660 in-lb
Recommended in-lb	
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Mounting Hardware	5/8-11 x 1" LG
One Wrench Installation	Y
Type	Cable or Tube to Insulator Bus Supports
UPC	781810283226
UPC 14 Digit GTIN	00781810283226

Dimensions

Bolt Circle Diameter	5 in
Dimension - B Length fraction	3-1/4 in
Dimension - G inch	4.50 in
Dimension - Height fraction	7-1/4 in
Dimension - Height inch	7.25 in
Dimension - Height mm	184.2 mm
Dimension - Hole Size fraction	11/16

Dimension - Hole Size inch	0.69 in
Dimension - Width fraction	7-1/2 in
Dimension - Width inch	7.50 in
Dimension - Width mm	191 mm

Conductor Related

Conductor - Connection Combination	Base to Tube
Conductor - Copper Tube EH Size	4 IPS
Conductor - Copper Tube EH Size Range	4 IPS
Conductor - Copper Tube Std Size	4 IPS
Conductor - Copper Tube Std Size Range	4 IPS
Conductor Type	• CU Tube Std-Size • CU Tube EH-Size
Number of Conductors	1

Certifications And Compliance

Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Carton Quantity	1
Minimum Pack Quantity	2

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section L - Bolted Substation](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SA..007374-01](#)
[Specifications - UH225](#)