



UHR153CG6, Substation Copper Bus Support

By Burndy
Catalog # [UHR153CG6](#)

Copper Bus Connectors

Features

- Type UHR Copper Bus Supports for Supporting Copper Cable or Tube to Base
- Suitable for mounting a wide range of cable or tube on post or pedestal type insulators
- Single bolt allows rotation to any angle
- Supplied with hardware for mounting to cap of insulator
- Suffix -B at the end of catalog denotes base mounting hardware is included

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Number Of Conductors	1
Conductor - Connection Combination	Base to Tube or Cable
Conductor - Copper Str Size Range	4/0 AWG-1250 kcmil
Conductor - Copper Str Size	• 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil • 800 kcmil • 850 kcmil • 900 kcmil



Conductor - Copper Tube Std Size Range	• 1000 kcmil • 1250 kcmil
Conductor - Copper Tube Std Size	• 1/4 IPS -1 IPS • 1/4 IPS • 3/8 IPS • 1/2 IPS • 3/4 IPS • 1 IPS

Configuration

Connector Type	Bus Support
----------------	-------------

Dimensions

Bolt Circle Diameter	3.00 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Hole Size fraction	9/16
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Hole Size inch	0.56 in

General

Plated	N
Material - Hardware UPC	DURIUM™ Silicon Bronze 621945159358
Type	Cable or Tube to Insulator Bus Supports
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	621945159358
UPC 14 Digit GTIN	00621945159358

Logistics

Minimum Pack Quantity	6
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)