



YA39AM2,750 kcmil Al, 2-Hole NEMA Spacing, AL9CU

By Burndy

Catalog # [YA39AM2](#)

750 kcmil, AL, 2-Hole, 1/2" Stud, 1.75" Spacing, AL9CU, Prefilled with oxide inhibitor, End Cap

Features

- UL486A-486B Listed and CSA Certified
- Aluminum terminals are dual rated to accommodate both copper and aluminum wire and are indicated with AL-CU on the connector - AL9CU is UL Listed 90°C, up to 35kV, AL7CU is UL Listed 75°C, up to 35kV
- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damage of the wire strands during insertion
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with wire size, die index, color code, and crimp location bands
- Factory pre-filled with PENETROX Type A13 oxide inhibitor
- Color coded end caps are factory inserted in the barrels to match the die color code and prevent foreign materials from entering the barrel
- Aluminum oxidation is not easily detected but causes resistance in a connection, it is imperative the proper preparation takes place prior to making an aluminum-to-aluminum connection

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	ALUMINUM / COPPER
Wire Size	• 700 KCMIL • 750 KCMIL
Conductor - AL Str Size	700 KCMIL-750 KCMIL
Conductor - AL Str Size Range	700 kcmil - 750 kcmil



Conductor - Copper Str Size	• 700 KCMIL • 750 KCMIL
Conductor Size	• 700 KCMIL • 750 KCMIL
Conductor Type	CODE
Conductor - Copper Str Size Range	700 kcmil - 750 kcmil

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	DUAL RATED


Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.69 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	186 mm
Dimension - Outside Diameter inch	1.60 in
Dimension - Thread Size	1/2
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56
Dimension - Strip Length inch	2 7/8
Dimension - Stud Size inch	1/2
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	2-9/16 in
Dimension - Z inch	0.74 in
Dimension - B Length inch	2.56 in
Dimension - D inch	3.12 in
Dimension - N inch	0.63 in
Dimension - Bolt Size inch	0.5

Dimension - Length Overall inch	7.31 in	Material	Aluminum
		Plating Type	Tin - Electro Plated
		Finish Type	Tin-Plated
		UPC 12 Digit	781810762004
		UPC 14 Digit GTIN	00781810762004
General		Logistics	
Trade Name	HYLUG™	Minimum Pack Quantity	1
Die Index	301	Carton Quantity	3
Feature - Barrel Type	Standard		
Feature - Barrel Style	Chamfered		
Plated	Y		
Color Code	Red		
Physical Attribute - Tongue Type	Standard		
Sub Brand	TERMINALS, HYLUG	Operational	
UPC	781810762004	Temperature Rating	194
Type	YA-A	Product Assets	



[Catalog \[English\]](#)